

## Software & Firmware

[More Info](#) | [Instructions](#) | [Get Quote](#)

Solinst always recommends using the latest software and firmware release.

Current releases can be downloaded at any time, free of charge, from the Solinst web site at: <https://downloads.solinst.com/>

Always use the latest Levellogger® PC Software version to install the latest Firmware versions.

**Note:** Solinst always recommends that our customers download the data from their AquaVent loggers, using the same Levellogger Software version they were originally programmed with.

## Operating System Requirements

Levellogger PC Software Versions 4.6.3 and up are compatible with Windows 10 & 11.



AquaVent	Levellogger PC Software	Firmware	SPX 5 Wellhead Firmware	SPX Wellhead Firmware	Solinst Levellogger App	SRU Firmware	DataGrabber Firmware
 <b>AquaVent 5 Logger</b>	4.7.0 <small>(Includes Firmware Upgrade Utility 1.7.0)</small>	1.006	 1.000	1.001	3.5.1 iOS 13.0, or later 	1.001 and up	DataGrabber 5: **Mk2 4.000 and up Mk1 3.002 (user-upgradable) 
 <b>AquaVent Logger</b>		1.000	1.000 As features differ slightly between models, it is recommended to use an SPX Wellhead with an AquaVent logger.	 1.000	3.0.1 Android 10.0 or higher  <small>*Note: Requires a Levellogger App Interface</small>		DataGrabber 5: Mk2: 4.00 and up Mk1: 3.002 DataGrabber: 2.000 to 3.002 (firmware version 2.000 and up is user-upgradable, below that, must be upgraded by Solinst)

**Note:** If both the Logger and Wellhead Firmware need to be updated, upgrade the Wellhead firmware first.

\*\*Mk2 DataGrabber 5 units sold starting October 2022; Mk1 units sold before then can only be upgraded to firmware 3.002.

## AquaVent Accessories

Wellhead Communication Cables, including USB Connector Cables, SD1-12 Connector Cables, and MODBUS RS232/RS485 Connector Cables, are compatible with all versions of the AquaVent Logger and applicable Communication Wellheads. Older style Vented Cables (sold before 4/16/21 with serial numbers lower than 506326) are not compatible with newer style AquaVent 5 Wellheads (sold after 5/7/21) or AquaVent 5 Loggers (sold after 4/5/21) without a small user modification – contact Solinst for instructions. Newer style Vented Cables are compatible with all versions of the AquaVent Logger – please note, after the new Vented Cable connector is fully tightened, the external o-ring on an old Logger or Wellhead is visible and it is normal not to seat against the connector.



Vented Cable



USB Connector Cable for Communication with a PC



Connector Cable to connect to an App Interface, SRU or DataGrabber



SDI-12 and MODBUS RS232/RS485 Connector Cables

\*Levellogger 5 App Interface



\*"Made for iPod," "Made for iPhone," and "Made for iPad" mean that an electronic accessory has been designed to connect specifically to iPod, iPhone, or iPad, respectively, and has been certified by the developer to meet Apple performance standards. Apple is not responsible for the operation of this device or its compliance with safety and regulatory standards. Please note that the use of this accessory with iPod, iPhone, or iPad may affect wireless performance.

©Apple, the Apple logo, iPhone, iPad, and iPod are trademarks of Apple Inc., registered in the U.S. and other countries. App Store is a service mark of Apple Inc. iOS is a trademark or registered trademark of Cisco in the U.S. and other countries and is used under license.

® Solinst is a registered trademark of Solinst Canada Ltd.

Android and Google Play are trademarks of Google Inc.